



# S19284HB, S19284JB

## Barrier-Free Cabinet-Mount Swing-Down Halo Eye and Eye/Face Wash Units

- Halo™ Delivers the Most Effective Eye/Face Washdown Coverage and Spray Pattern
- Exceeds American National Standard Z358.1 Specifications
- Durable, Ceramic Valve
- Precise 20° Swing-Down Activation
- Compact, Concealed Unit
- Designed to Mount Between Standard 16" Wall Studs
- Chrome-Plated Brass on Exposed Piping and Fittings
- Fully-Assembled and Factory-Tested Eyewash or Eye/Face Wash with Hinged Dust Covers
- Universal Identification Sign and Inspection Tag Included
- Halo is Covered by One or More of the Following Patents: 9,700,484; 9,314,398; D662220; D673298; D662605; D685920. Other Patents Pending.



### Specifications

Barrier-free design makes this eye and eye/face wash fully accessible to people with physical disabilities. Unit design saves space and fits easily into any work environment. Especially ideal for areas where space is limited. Halo eye/face wash provides effective wash down coverage and spray pattern. Integral strainer reduces debris in the water and also prevents clogging. Units operate quickly by pulling swing arm 90° over floor drain. New vandal resistant ceramic valve limits wear and tear on moving parts, providing dependability and long lasting performance. Safe, steady water flow under varying water supply conditions from 30-90 PSI is assured by integral flow control. Unit is flush-mounted in the wall.

#### Rough-Ins:

S19284HB and S19284JB require a rough wall opening of 14½"W x 30¼"H x 4"D.



*This plumbing fixture is not intended to dispense water for human consumption through drinking or for preparation of food or beverages.*

### Standard Equipment

#### Wall Cabinet

Wall cabinet is stainless steel. Brass stop-valve, tailpiece, and fittings are concealed behind a locked, hinged door for easy access.

#### Eyewash

The Halo eyewash system offers a high performance rinsing platform that provides rapid relief to an individual's eyes that have been injured by chemicals or particulate. The eyewash includes an integral 5.1 gpm flow control providing water at a safe velocity while maintaining its effectiveness (exceeds minimum water flow of 0.4 GPM at 30 PSI). Safe, steady water flow under varying water supply conditions from 30–90 PSI is assured by integral flow control in the sprayhead assembly.

#### Eye/Face Wash

The Halo eye/face wash system offers a high performance rinsing platform that provides rapid relief to an individual's eyes and face that have been injured by chemicals or particulate. This system provides the most complete face wash available in the market. The eye/face wash includes an integral 5.1 gpm flow control providing water at a safe velocity while maintaining its effectiveness (exceeds minimum water flow of 3.0 GPM at 30 PSI). Safe, steady water flow under varying water supply conditions from 30-90 PSI is assured by integral flow control in the sprayhead assembly.

#### Valve

Ceramic ½" NPT stay-open valve. The ceramic discs provide a precise 20° activation and deactivation angle, minimizing excessive splashing when the unit is activated.

#### Pipe and Fittings

Chrome-plated brass.

#### Water Supply

½" NPT.



Model	Description
<input type="checkbox"/> S19284HB	Barrier-Free Cabinet-Mount Swing-Down Halo Eyewash Unit
<input type="checkbox"/> S19284JB	Barrier-Free Cabinet-Mount Swing-Down Halo Eye/Face Wash Unit
<input type="checkbox"/> S19-2000	Navigator EFX8 - Emergency Thermostatic Mixing Valve

### Tepid Water Options

[Navigator S19-2000 EFX8 Emergency Thermostatic Mixing Valve](#)

[Keltech CLE-Series Tankless Water Heater](#)


Satisfies ANSI/ISEA Z358.1 tepid water requirements.



# S19284HB, S19284JB

## Barrier-Free Cabinet-Mount Swing-Down Halo Eye and Eye/Face Wash Units

### S19284HB Dimensions





# S19284HB, S19284JB

## Barrier-Free Cabinet-Mount Swing-Down Halo Eye and Eye/Face Wash Units

### S19284JB Dimensions

